



PXX-A



PXCS

## ● 使用例



## ● 型号指定

## PXCS-12-14-6



- 请与分度柱塞组合使用。
- 即使安装部壁厚较薄，也可稳妥固定。
- 选型方法

请确保分度柱塞用轴环 **PXCS** 的外径D及内径d满足以下条件。

$D \leq D_1$  (使用分度柱塞的六角对角尺寸)

$d = M$  (使用分度柱塞的螺纹公称直径)

选型示例： **PXX-5-A** 时

$D_1$  : 13.8

M : 10

适用轴环为 **PXCS-10-12**。

- 材质、表面处理



	PXCS
主体	SUS303

## 尺寸

单位：mm

型号	d <b>1</b>	D <b>2</b>	质量 (g)
PXCS-6-7	6	7	0.2 - 0.6
PXCS-8-10	8	10	0.4 - 2.2
PXCS-10-12	10	12	0.5 - 3.2
PXCS-12-14	12	14	0.6 - 4.5
PXCS-12-17	12	17	1.8 - 11
PXCS-16-17	16	17	0.4 - 2.4
PXCS-16-19	16	19	1.3 - 7.7
PXCS-20-22	20	22	3.1 - 9.4

型号	t (mm) <b>3</b>										
	2	4	5	6	8	10	12	14	16	18	
PXCS-6-7	●	●		●	●						
PXCS-8-10	●	●		●	●	●					
PXCS-10-12	●	●		●	●	●	●				
PXCS-12-14	●	●		●	●	●	●	●			
PXCS-12-17	●	●	●	●	●	●	●				
PXCS-16-17	●	●		●	●	●	●				
PXCS-16-19	●	●		●	●	●	●				
PXCS-20-22				●	●	●	●	●	●	●	